


The Timken Company

4500 Mt Pleasant St. NW

N. Canton, OH 44720

Phone: (234) 262-3000

E-Mail: CustomerCAD@timken.com • **Web site:** www.timken.com

Part Number 6211-2RS-C3, Deep Groove Ball Bearings (6000, 6200, 6300, 6400)

Timken's deep groove ball bearings deliver reliable performance in a wide range of applications and conditions. With super-finished raceways and controlled geometries, our premium design helps ensure consistent quality.



[Key Dimensions](#) | [Dimensions](#) | [Basic Load Ratings](#) | [Factors](#)

Key Dimensions

| | |
|---------------------|---------------|
| Clearance | C3 |
| Bore Size d | 55 mm |
| Features | Contact Seals |
| Bearing Type | Standard DGBB |

Dimensions

| | |
|-----------------------------|--------|
| Outside Diameter D | 100 mm |
| Outside Ring Width B | 21 mm |
| Radius Rs min | 1.5 mm |



Basic Load Ratings


| | |
|---------------------------------|---------|
| Cr - Dynamic Load Rating | 43400 N |
|---------------------------------|---------|

| | |
|---------------------------------|---------|
| C0r - Static Load Rating | 29200 N |
|---------------------------------|---------|

Factors

| | |
|-------------------------------|----------|
| Grease Reference Speed | 4300 rpm |
|-------------------------------|----------|

| | |
|----------------------------|-----------|
| Oil Reference Speed | 10000 rpm |
|----------------------------|-----------|



METRIC UNITS

Weight 0.61 kg

TIMKEN®

THE TIMKEN COMPANY
NORTH CANTON, OHIO USA

6211-2RS-C3
Deep Groove Ball Bearings (6000, 6200, 6300, 6400)

Dynamic Load Rating 43400 N
Static Load Rating 29200 N

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

FOR DISCUSSION ONLY