

After the bushes have been pressed into a H7 housing hole using an m6 mandrel, cylindrical bushes have an H7 inside diameter (H8 for  $\varnothing \geq 50$  mm) and flanged bushes have an H8 inside bush diameter .

Delivery tolerance in accordance with ISO standard F7/s7 for cylindrical bushes (for  $D_i > 50$  mm and  $D_o > 50$  mm F8/s8) and F8/s8 for flanged bushes.