


The Timken Company

4500 Mt Pleasant St. NW


N. Canton, OH 44720

Phone: (234) 262-3000

E-Mail: CustomerCAD@timken.com • **Web site:** www.timken.com

UCF 200 Four-Bolt Flanged Mounted Bearings - Set Screw Locking

- UCF four-bolt flanged units are suggested for industrial applications where normal loads are encountered.
- Each unit comes assembled and ready for mounting, using bolts through the flange.
- These units use wide inner ring ball bearings with self-aligning spherical outside diameters that compensate for shaft misalignment.
- Timken UCF series Mounted Bearings feature the Timken set screw locking (UC) bearing insert.
- Bearing prelubricated and ready for immediate installation.

[more](#)


1 2 3

<u>Part Number</u>	<u>Bearing Number</u>	<u>Shaft Size d</u>	<u>Static Load Rating</u>	<u>Dynamic Load Rating</u>	<u>CAD</u>
<u>UCF201</u>	UC201	12 mm	6650 N 1495 lbf	12800 N 2878 lbf	
<u>UCF201-8</u>	UC201-8	1/2 in	6650 N 1495 lbf	12800 N 2878 lbf	
<u>UCF202</u>	UC202	15 mm	6650 N 1495 lbf	12800 N 2878 lbf	
<u>UCF202-10</u>	UC202-10	5/8 in	6650 N 1495 lbf	12800 N 2878 lbf	
 <u>UC203</u>	UC203	17 mm	6650 N 1495 lbf	12800 N 2878 lbf	

<u>Part Number</u>	<u>Bearing Number</u>	<u>Shaft Size d</u>	<u>Static Load Rating</u>	<u>Dynamic Load Rating</u>	<u>CAD</u>
<u>UCF204-12</u>	UC204-12	3/4 in	6650 N 1495 lbf	12800 N 2878 lbf	
<u>UCF204</u>	UC204	20 mm	6650 N 1495 lbf	12800 N 2878 lbf	
<u>UCF205-14</u>	UC205-14	7/8 in	7850 N 1765 lbf	14000 N 3147 lbf	
<u>UCF205-15</u>	UC205-15	15/16 in	7850 N 1765 lbf	14000 N 3147 lbf	
<u>UCF205</u>	UC205	25 mm	7850 N 1765 lbf	14000 N 3147 lbf	
<u>UCF205-16</u>	UC205-16	1 in	7850 N 1765 lbf	14000 N 3147 lbf	
<u>UCF206-18</u>	UC206-18	1 1/8 in	11300 N 2540 lbf	19500 N 4385 lbf	
<u>UCF206</u>	UC206	30 mm	11300 N 2540 lbf	19500 N 4385 lbf	
<u>UCF206-19</u>	UC206-19	1 3/16 in	11300 N 2540 lbf	19500 N 4385 lbf	
<u>UCF207-20</u>	UC207-20	1 1/4 in	15400 N 3462 lbf	25700 N 5778 lbf	
<u>UCF206-20</u>	UC206-20	1 1/4 in	11300 N 2540 lbf	19500 N 4385 lbf	
<u>UCF207-21</u>	UC207-21	1 5/16 in	15400 N 3462 lbf	25700 N 5778 lbf	
<u>UCF207-22</u>	UC207-22	1 3/8 in	15400 N 3462 lbf	25700 N 5778 lbf	
<u>UCF207</u>	UC207	35 mm	15400 N 3462 lbf	25700 N 5778 lbf	
<u>UCF207-23</u>	UC207-23	1 7/16 in	15400 N 3462 lbf	25700 N 5778 lbf	

<u>Part Number</u>	<u>Bearing Number</u>	<u>Shaft Size d</u>	<u>Static Load Rating</u>	<u>Dynamic Load Rating</u>	<u>CAD</u>
<u>UCF208-24</u>	UC208-24	1 1/2 in	17800 N 4002 lbf	29100 N 6542 lbf	
<u>UCF208-25</u>	UC208-25	1 9/16 in	17800 N 4002 lbf	29100 N 6542 lbf	
<u>UCF208</u>	UC208	40 mm	17800 N 4002 lbf	29100 N 6542 lbf	
<u>UCF209-26</u>	UC209-26	1 5/8 in	21300 N 4788 lbf	34100 N 7666 lbf	
<u>UCF209-27</u>	UC209-27	1 11/16 in	21300 N 4788 lbf	34100 N 7666 lbf	
					1 2 3