


The Timken Company

4500 Mt Pleasant St. NW


N. Canton, OH 44720

Phone: (234) 262-3000

E-Mail: CustomerCAD@timken.com • **Web site:** www.timken.com

Part Number 22312KEJW33, Spherical Roller Bearings - Steel Cage

Spherical bearings are designed to manage high radial loads even when misalignment, poor lubrication, contamination, extreme speeds or critical application stresses are present.



[Specifications](#) | [Factors](#) | [Dimensions](#) | [Abutment and Fillet Dimensions](#) | [Basic Load Ratings](#)

Specifications

UPC Code 087796023956

Design Unit Metric

d - Bore 60 mm

Lubrication Type Standard Grease

Bore_Taper 1/12

Cage Type EJ

Cage Material Steel

Superseded Part 22312KCJW33



e - ISO Factor¹	0.34
Y0 - ISO Factor²	1.93
Y1 - ISO Factor³	1.98
Y2 - ISO Factor⁴	2.94
Reference Thermal Speed Rating (Grease)	4000 rpm
Reference Thermal Speed Rating (Oil)⁵	4700 rpm
Cg - Geometry Factor⁶	0.0532

Dimensions

D - Outer Diameter	130 mm 5.1181 in
B' - Inner Ring Width	46 mm 1.811 in
B - Outer Ring Width	46 mm 1.811 in

Abutment and Fillet Dimensions

R - Inner Ring "To Clear" Radius⁷	2 mm 0.080 in
r - Outer Ring "To Clear" Radius⁸	2 mm 0.08 in
da - Inner Ring Backing Diameter	77 mm 3.000 in
Da - Outer Ring Backing Diameter	117 mm 4.600 in

Basic Load Ratings

C0 - Static Radial Rating	307000 N 69000 lbf
----------------------------------	-----------------------

C1(2) - Dynamic Radial Rating (Two-Rows)	306000 N 68800 lbf
---	-----------------------

¹ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

² These factors apply for both inch and metric calculations. See engineering

³ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.


⁴ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁵ See thermal speed ratings in the engineering section.

⁶ Geometry constant for Lubrication Life Adjustment Factor a_3 .

⁷ Maximum housing fillet radius that bearing corners will clear.

⁸ These maximum fillet radii will be cleared by the bearing corners.



METRIC UNITS

Number of Rollers Per Row	14
ISO Factor e	0.34
ISO Factor Y0	1.93
ISO Factor Y1	1.98
ISO Factor Y2	2.94
Bearing Weight	kg
Cage Type	EJ
Cage Material	Steel
Bore Taper	1/12

TIMKEN®

THE TIMKEN COMPANY
NORTH CANTON, OHIO USA

22312KEJW33
SRB ASSEMBLY

Dynamic Radial Rating (Two Rows)	306000	N
Static Radial Rating	307000	N

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

FOR DISCUSSION ONLY